## 

MaxiCut<sup>®</sup> Ultra<sup>™</sup> 58-917 is the naked liner used on the coated MaxiCut<sup>®</sup> Ultra<sup>™</sup> series. As an uncoated underglove it provides cut resistance when used underneath a disposable or other waterproof gloves.

As with all our gloves MaxiCut<sup>®</sup> Ultra<sup>™</sup> is dermatologically accredited by the Skin Health Alliance as part of our HandCare<sup>™</sup> program. They are also pre-washed prior to packaging enabling us to guarantee them "Fresh out of the pack" as certified by Oeko-Tex<sup>®</sup>.

MaxiCut<sup>®</sup> Ultra<sup>™</sup> 58-917 is compliant to FDA CFR Title 21 Part 177.

## FOR PROTECTION AGAINST CUTS

**CUTtech**<sup>®</sup> combines and blends high performance yarns and fibres to impart different levels of cut protection with the driving philosophy to deliver high levels of comfort and wearer satisfaction.

We only source our fibre requirements from long term key partners. Once in-house, they are covered, twisted and plated at our production facility, the end result being innovative yarns and fibres that are light yet flexible. They are engineered to perform.



## FOR REDUCED HAND FATIGUE

**ERGOtech**<sup>®</sup> focuses on making the glove work like a second skin. ERGOtech<sup>®</sup> concentrates on maximizing the form, fit and feel of our gloves, which results in a superior user experience.

Fitting like a second skin this glove is perfect for donning and doffing an overglove.

ERGOtech<sup>®</sup> is designed, developed and integrated into our gloves to mimic the natural contours of the hand, to deliver ourstanding flexibility, dexterity and tactile sensitivity.







The Skin Health Alliance has awarded professional dermatological accreditation following review of the scientific dossier behind this product. View www.skinhealthalliance.org.



This glove has been laundered prior to final packaging making it clean and safe for use.



All ingredients used in the manufacturing and construction of this product are compliant with the REACH legislation.



The Oeko-Tex<sup>®</sup> Association has evaluated and certified this product as skin safe from the second it comes into contact with the skin.

More information about HandCare<sup>™</sup> by ATG<sup>®</sup> is available at **www.atg-glovesolutions.com**.



proRange™

## 

| Glove          |                 | Sleeve                        |  |
|----------------|-----------------|-------------------------------|--|
|                | 58-917          | 89-5730<br>89-5740<br>89-5745 |  |
| Coating        | -               | -                             |  |
| Color          | -               | -                             |  |
| Liner          | Light blue      | Light blue                    |  |
| Sizes          | 7(S) to 11(XXL) | Standard                      |  |
| Palm thickness | 0,80 mm         | -                             |  |
| Length         | 26 cm           | 30/40/45 cm                   |  |
| EN 388 📛       | 3542            | 3542                          |  |
| Food contact   | FDA compliant   | -                             |  |
| Silicon free   | yes             | -                             |  |

Where to use

Cut resistant glove for wearing under disposable gloves or other waterproof gloves.

The glove can be laundred by 40°C.





MaxiCut<sup>®</sup> Ultra<sup>™</sup> 44-3745 MaxiCut<sup>®</sup> Ultra<sup>™</sup> combines cut protection with comfort, flexibility and dexterity for dry environments.



MaxiCut® Ultra™ 44-3745 (3/4 dipped)



**MaxiCut**<sup>®</sup> Ultra<sup>™</sup> 44-3445 (Palm dipped with dots) Offers increased cushioned for those doing repetitive jobs or carrying heavy loads.



MaxiCut® Ultra™ 44-3445 (3/4dipped with dots)



